


KEMET, ZCT, Current, Round - Toroidal, Zero Phase, High Sensitivity, Compact



General Information	
Series:	ZCT
Type:	Current
Style:	Round - Toroidal
Description:	Zero-Phase Current Transformers
Features:	High Sensitivity, Compact
Lead:	Cables
RoHS:	Yes
Notes:	Measurement Conditions: f=60Hz, R=300 Ohms, I _o =22.5 mAmps

Dimensions	
D	16.5mm MIN
H	10.8mm MAX
D2	32mm MAX
D3	34.5mm MAX
D4	7mm NOM
LL	67mm +/-3mm

Specifications	
Temperature Range:	-20/+80C
Voltage DC:	8 mV MIN (Output)
Current:	125 Amps
Resistance:	30 Ohms
Miscellaneous:	Overinput characteristics (After DC5A input) = 10% MAX

Packaging Specifications	
Packaging:	Tray
Packaging Quantity:	300
Weight:	16.5 g