


KEMET Part Number: MPCG1040LR88 **Not for New Design**
(UPIB1040LR8800)

KEMET, MPCG, Power, 880 nH, 20%



Dimensions

Chip Size	4539
L	11.5mm MAX
W	10mm +/-0.3mm
T	4mm MAX
LL	2.1mm NOM
G	3.5mm +/-0.5mm

Packaging Specifications

Packaging:	T&R, 330mm
Packaging Quantity:	500

General Information

Series:	MPCG
Style:	SMD
Description:	Shielded, Surface Mount Inductor
Features:	High Speed, Large Current DC/DC Converter
RoHS:	Yes
Core:	Composite

Specifications

Inductance:	0.88 uH (0.1 MHz)
Inductance Tolerance:	20%
Temperature Range:	-40/+125C
Rated Temperature:	120C
Shielded:	Yes
Current:	19 Amps (Isat, 20% Drop In Inductance), 17 Amps (Irms, 40C Rise By Self Heating)
DC Resistance:	2.3 mOhms