


KEMET, L-PWF, Power, 10 uH, 10%



Dimensions	
Chip Size	0603
L	1.6mm +/-0.1mm
W	0.8mm +/-0.1mm
T	0.8mm +/-0.1mm
LL	0.35mm +/-0.2mm

Packaging Specifications	
Packaging:	T&R
Packaging Quantity:	3000

General Information	
Series:	L-PWF
Style:	SMD Chip
Description:	Surface Mount Inductor
Features:	Bottom Surface Electrode
RoHS:	Yes

Specifications	
Inductance:	10 uH (2.52 MHz)
Inductance Tolerance:	10%
Temperature Range:	-40/+105C
Current:	200 mAmps (MAX)
DC Resistance:	1.2 Ohms
Self-Resonant Frequency:	40 MHz