


KEMET, SCR25, AC Line Filters, Common Mode, 800 uH



Dimensions	
D	35mm MAX
L	35mm MAX
T	33mm MAX
H	26mm MAX
LL	5mm +/-2mm
S	11mm NOM

Packaging Specifications	
Packaging:	Tray
Packaging Quantity:	140
Weight:	45 g

General Information	
Series:	SCR25
Style:	Through-Hole
Features:	High Impedance, Space Saving
RoHS:	Yes
Miscellaneous:	66 (K) Temperature Rise Max.

Specifications	
Voltage AC:	250 VAC
Inductance:	0.8 mH
Current:	20 A
Temperature Range:	-25/+120C
DC Resistance:	4.7 mOhms