


KEMET, SCR25, AC Line Filters, Common Mode, 3500 uH



General Information	
Series:	SCR25
Style:	Through-Hole
Features:	High Impedance, Space Saving
RoHS:	Yes
Miscellaneous:	70 (K) Temperature Rise Max.

Specifications	
Voltage AC:	250 VAC
Inductance:	3.5 mH
Current:	10.5 A
Temperature Range:	-25/+120C
DC Resistance:	17 mOhms

Dimensions	
D	35mm MAX
L	35mm MAX
T	33mm MAX
H	26mm MAX
LL	5mm +/-2mm
S	11mm NOM

Packaging Specifications	
Packaging:	Tray
Packaging Quantity:	140
Weight:	49 g

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.