


Star-quad Shielded Multiconductor Microphone Cable

pro-POWER



Specifications

Conductor	: 30/0.08mm BC OFC
Insulation	: PE
Insulation Dia.	: 1 ±0.01mm/0.25mm ±0.08mm
Colour	: Black, Red, Blue and Transparent
Filler	: Cotton yarn
Wrap	: Tissue paper
Shield	: SP73/0.12mm BF OFC coverage 77%
Jacket	: PVC
Colour	: Black
Size	: 4.8 ±0.15mm / 1.02 ±0.15mm
Wall Thickness	: ≈0.5mm

Electric data at 20°C

Conductor Resistance	: 126.05Ω/km
----------------------	--------------

Part Number Table

Description	Packing	Part Number
Star-quad Shielded Multiconductor Microphone Cable	100m Plastic Spool	24-14430

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-POWER is the registered trademark of the Group. © Premier Farnell Limited 2016.

www.element14.com
www.farnell.com
www.newark.com
www.cpc.co.uk

pro-POWER