



# Structured Cable Products™

Quality Installations Deserve Quality Products

www.scpcat5e.com  
 sales@scpcat5e.com  
 Direct: 954-327-5770  
 Toll Free: 866-470-5742

**SCP PART#: 18/2SH-GY**

UPC: 810070010706

**DESCRIPTION:**

Shielded Riser 2/C 18/16 AWG SBC, PVC Insulation, Gray PVC Riser Jacket, 1000 FEET/305M

**General Specification of Product :**

<b>Final Diameter :</b>	0.166 inches	4.216 mm
<b>Total Cable Weight:</b>	38 kg/km	26 lbs/1000 ft
<b>Conductor :</b>	18 AWG 16 x.010 Bare Copper	
<b>Insulation :</b>	PVC	
<b>Shield :</b>	Foil Shield 0.625	
<b>Drain \ Ground:</b>	24 AWG 7 Strand STC Cond.	
<b>Outer Jacket :</b>	PVC	

**Print Notes :** Sequentially marked per 2FT (0 - infinity)

**Standard Print :** STRUCTURED CABLE PRODUCTS --- P/N 18/2SH --- (UL) CL3R  
 E198137-SCP (UL) C(UL) CMR SHIELDED 2/C 18 AWG --- ZONE/DEVICE A B  
 C D E 0 1 2 3 4 5 6 7 8 9 RoHS

**Electrical Characteristics :**

DC Resistance 25°C:	6.7 Ohms / 1000 ft
Mutual Capacitance :	69 pF/ft
Cond to Shield Cap. :	125.4 pF/ft
Impedance :	40 Ohms
Velocity of Prop :	68 %
Inductance. :	1.3 mH/km

**Additional Information :**

Cabled OD Avg: 0.115  
 Ins Thickness: 0.010  
 Jkt Thickness: 0.015  
 Certified: UL CL3R / UL C(UL) CMR  
 Flame Rating: Riser  
 Max Voltage: 300V  
 Packaging: Reelex Box 12.5 x 12.5 x 8"  
 Packaged: 26 lbs / 12 kgs

( All of the above values are approximated to within +/- 10% )

**QMS Registered ISO 9001**

3091802.10R.1000