



# Structured Cable Products™

Quality Installations Deserve Quality Products

www.scpcat5e.com  
 sales@scpcat5e.com  
 Direct: 954-327-5770  
 Toll Free: 866-470-5742

**SCP PART#: 18/4-WT-500**

UPC: 810070018276

**DESCRIPTION:**

Unsh Riser 4/C 18/16 AWG SBC, PVC Insulation, White PVC Riser Jacket, 500 FEET/152M

**General Specification of Product :**

<b>Final Diameter :</b>	0.192 inches	4.877 mm
<b>Total Cable Weight:</b>	52 kg/km	35 lbs/1000 ft
<b>Conductor :</b>	18 AWG 16 x.010 Bare Copper	
<b>Insulation :</b>	PVC	
<b>Outer Jacket :</b>	PVC	

**Print Notes :** Sequentially marked per 2FT (0 - infinity)

**Standard Print :** STRUCTURED CABLE PRODUCTS - - - P/N 18/4 - - - (UL) CL3R E198137-SCP  
 (UL) C(UL) CMR UNSH 4/C 18 AWG - - - ZONE/DEVICE A B C D E 0 1 2 3 4 5 6  
 7 8 9 RoHS

**Electrical Characteristics :**

DC Resistance 25°C:	6.6 Ohms / 1000 ft	
Mutual Capacitance :	25.3 pF/ft	
Impedance :	75 Ohms	
Velocity of Prop :	64 %	
Inductance. :	1.2 mH/km	

**Additional Information :**

Cabled OD Avg: 0.151  
 Ins Thickness: 0.010  
 Jkt Thickness: 0.016  
 Certified: UL CL3R / UL C(UL) CMR  
 Flame Rating: Riser  
 Max Voltage: 300V  
 Packagin: Reelex Box 12.5 x 12.5 x 8"  
 Packaged Weight: 18 lbs / 8 kgs

( All of the above values are approximated to within +/- 10% )

**QMS Registered ISO 9001**

3071804.02R.500

UNCONTROLLED COPY SpecSheets.rpt

Part Spec Rev: 2 06/10/15