

SCP → Structured Cable Products

SCP Specification Sheet

Date: 09-2007

Rev Date: 05-2014

Structured Product#: **22/2SOL-COIL-WT**

Description: **2C/22 AWG SOLID COPPER PVC COIL PACK- WHITE- 500 FT**

Conductor	22 AWG BARE COPPER
Conductor Stranding	Solid
Nom Cond DC Resistance, ohms/1000 ft	18
Insulating Material Type	PVC Riser
Insulation Wall Thickness, inches	0.006
Conductor Insulated O.D., inches	0.039
Jacket Wall Thickness , inches	0.015
Jacket Material Type	PVC Riser
Finished Cable O.D. , inches	0.072 x 0.107
Total Cable Weight (lbs/1000 ft)	7.0
Voltage Rating (Volts)	300
Overall Temperature Rating (degrees Celsius)	75
Nominal Mutual Capacitance, pF/ft	21
Nominal Impedance (ohms)	86
RoHS Compliant	Yes
Packaging Weight	3.50 LBS / 1.59 KGS

(All of the above values are approximated to within 10%)

*** Put-ups available in any length required.**

Product also available in Coils, Reelex Boxes, Spools, etc.