

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1062250014](#)
Status: **Active**
Overview: [Optical Connectivity Solutions](#)
Description: MPO Female-to-MPO Female Trunk Cable Assembly, 50/125µm, 5.40mm, Multimode, 12 Fiber, Plenum, OM3, 25.0m Length, Aqua

Documents:

[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Fiber Optic Assemblies
Series	106225
Boot Type	Straight
Connector to Connector	MPO-to-MPO
Mode	Multimode
Overview	Optical Connectivity Solutions
Product Literature Order No	987651-6181
Product Name	MPO
UPC	191128250269


Physical

Cable Length	25.0m
Cable Size	5.40mm
Fiber (Core/Cladding)	50/125µm
Net Weight	878.141/g
Single Ended	No
Wire/Cable Type	12 Fiber OM3 Plenum

Material Info

Reference - Drawing Numbers

Sales Drawing	1062250013-000
---------------	----------------



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[106225 Series](#)