

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1062250015](#)  
**Status:** **Active**  
**Overview:** [Optical Connectivity Solutions](#)  
**Description:** MPO Female-to-MPO Female Trunk Cable Assembly, 50/125µm, 5.40mm, Multimode, 12 Fiber, Plenum, OM3, 50.0m Length, Aqua

**Documents:**

[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)  
[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Fiber Optic Assemblies
Series	<a href="#">106225</a>
Boot Type	Straight
Connector to Connector	MPO-to-MPO
Mode	Multimode
Overview	<a href="#">Optical Connectivity Solutions</a>
Product Literature Order No	987651-6181
Product Name	MPO
UPC	191128250276


**Physical**

Cable Length	50.0m
Cable Size	5.40mm
Fiber (Core/Cladding)	50/125µm
Net Weight	1722.006/g
Single Ended	No
Wire/Cable Type	12 Fiber OM3 Plenum

**Material Info**

**Reference - Drawing Numbers**

Sales Drawing	1062250013-000
---------------	----------------



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ED/61/2018 (27 June  
2018)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[106225 Series](#)