



## **Live On The Edge**

The Rift is a high-performance Mid-Tower gaming case with a stylish edge design RGB LED strip displaying 13 unique lighting modes, 6 RGB flow and 7 static colour modes. Mesh vents on the bottom-right side of the front panel increases air flow and circulation. Comes equipped with a full acrylic side panel to showcase the inside of your rig. Supports liquid cooling.

### **Key Features**



## AIR COOLING

Supports air cooling in the front, top, and rear of the case to enhance cooling performance.

- Front: 120mm x 3 (Optional)
- Top: 120mm x 1 (Optional)
- Rear: 120mm x 1 (Includes 120mm Fan)
- Supports VGA Fan: 120mm x 2 (Optional)

## LIQUID COOLING

Supports liquid cooling in the front panel.

- Front: 120mm Radiator (Optional)



## AIR COOLING

Supports air cooling in the front, top, and rear of the case to enhance cooling performance.

- Front: 120mm x 3 (Optional)
- Top: 120mm x 1 (Optional)
- Rear: 120mm x 1 (Includes 120mm Fan)
- Supports VGA Fan: 120mm x 2 (Optional)

## LIQUID COOLING

Supports liquid cooling in the front panel.

- Front: 120mm Radiator (Optional)



## COOLING FOR YOUR GRAPHICS CARDS

Supports graphics card cooling: 2 x 120mm fans for superior VGA cooling.



## BUILT FOR HIGH PERFORMANCE

- Supports CPU cooler up to a max. height of 152mm
- Supports longer high-end graphics cards up to 340mm / 371mm (without front fan)
- Supports ATX power supply up to 180mm



## BUILT FOR HIGH PERFORMANCE

- Supports CPU cooler up to a max. height of 152mm
- Supports longer high-end graphics cards up to 340mm / 371mm (without front fan)
- Supports ATX power supply up to 180mm



## CONVENIENT ACCESS TO YOUR MEDIA

Quick and easy access to SAS control switch, 1 x 3.0 USB 2.0, 2 x 3.0 USB, HD audio and two ports, and power button.

Supports memory card reader from the top panel:  
SD, microSD (3.5mm), SDHC, microSDHC up to 64GB, SDXC, microSDXC up to 256GB.





## Key Features

- **Bring Your Case to Life** - Unique edge design LED lighting on the left side of the front panel gives this case a stylish look and feel. Comes equipped with 13 preset lighting modes: 6 RGB flow lighting modes and 7 Static colour modes.
- **Improved Air Ventilation** - Mesh vents on the bottom-right side of the front panel increases air flow and circulation.
- **Full Acrylic Side Panel** - Comes with a full acrylic side panel to showcase the inside of your rig.
- **Dual Chamber Design** - Built with a dual chamber design to direct heat away from the main chamber for more effective all-around cooling.
- **Air Cooling** - Supports air cooling in the front, top and rear of the case to enhance cooling performance. Front: 120mm x 3 (Optional), Top: 120mm x 1 (Optional) and Rear: 120mm x 1 (Includes 120mm Fan). Supports VGA Fan: 120mm x 2 (Optional).
- **Liquid Cooling** - Supports liquid cooling in the front panel. Front: 120mm Radiator (Optional).
- **Cooling for Your Graphics Card** - Supports graphics card cooling: 2 x 120mm fans for superior VGA cooling.
- **Built for High Performance** - Supports CPU cooler up to a max. height of 155mm. Supports longer high-end graphics cards up to 346mm / 371mm (without front fan). Supports ATX power supply up to 180mm.
- **Convenient Access to Your Media** - Quick and easy access to LED control switch, 1 x 3.0 USB, 2 x 2.0 USB, HD audio and mic ports + power button. Supports memory card reader from the top panel: SD, microSD (T-Flash), SDHC, microSDHC up to 64GB, SDXC, microSDXC up to 32GB.
- **Storage Capability** - Supports up to 2 x 3.5" HDDs and 5 x 2.5" HDDs/SSDs.
- **Easy Maintenance** - Removable dust filters on the top and bottom of the case for fast and convenient cleaning.

## Specifications

**Chassis  
Dimensions  
(Excluding (D) 375 x (H) 430 x (W) 184mm  
Fascia /  
Panels):**

## Case Specifications

**Form Factor:** Midi Tower  
**Motherboard Support:** ATX, Micro ATX, Mini ITX  
**PSU Support:** Standard ATX  
**PSU Location:** Bottom  
**Gaming Case:** Yes  
Water Cooling Ready!  
**Water Cooling:** Supported Radiator Size: **120mm**  
Supported Radiator Positions: **Front**  
**Body Material:** 0.5mm SPCC  
**Front Bezel Material:** ABS  
**Side Panel:** Acrylic Side Window  
**Internal Cable Management Depth:** 20mm  
**External Bays:**  
**Internal Bays:** 2 x 3.5" Internal  
5 x 2.5" Internal  
**Drive Bay Notes:**  
**Expansion Slots:** 7 x Full Size  
**Cooling Front:** Space for 3 x 12cm Fan (Not Included)  
**Cooling Top:** Space for 1 x 12cm Fan (Not Included)  
**Cooling Rear:** 1 x 12cm Fan (Included)  
**Cooling Side:** None  
**Cooling Bottom:** Space for 2 x 12cm Fan for VGA cooling (Not Included)  
**Fan Controllers:** 0 Fan Controllers, controlling up to 0 fans in total  
1 x USB 3.0  
2 x USB 2.0  
**IO Ports:** 1 x HD Audio  
1 x Microphone  
SD/TF Card Reader Included (Built-in)  
**GPU Max Length:** 371mm  
**CPU Cooler Maximum Height:** 155mm  
**Front Bezel Colour:** Black  
**Body Colour:** Black  
**System Cabinet Features:**  
**PSU Included:** No

### **General Specifications**

**Manufacturer Part Number:** ACCM-PV13012.11  
**EAN Number:** 4718009153134  
**Has Mains Plug:** No  
**Colour:** Black  
**What's In The Box:** Case  
Manual  
Screws  
**Unit (Product) Dimensions (mm):** 200mm x 447mm x 425mm (W x H x D)  
**Packaging Dimensions (mm):** 231mm x 478mm x 483mm (W x H x D)  
**Net Weight (KGs):** 3.9 KGs

**Gross Weight** 4.8 KGs  
**(KGs):**