

Main Specifications

Screen Size	21.5
Resolution (max.)	1920x1080

All Specifications

Display

Screen Size	21.5
Panel Type	IPS
Backlight Technology	LED backlight
Resolution (max.)	1920x1080
Brightness	250
Native Contrast(typ.)	1000:1
Viewing Angle (L/R;U/D) (CR \geq 10)	178/178
Response Time	5ms (GtG)
Refresh Rate	60Hz
Aspect Ratio	16:9
Display Colors	16.7 million colors
Color Gamut	72% NTSC
Display Area(mm)	476.06 x 267.79
PPI	102
DCR (Dynamic Contrast Ratio) (typ.)	20,000,000 : 1
Color Bit	8 bit

Audio

Built-in Speaker	1Wx2
Headphone Jack	Yes

Audio Line In	Yes
---------------	-----

Monitor

Product Color	Black
---------------	-------

Color Temperature	Reddish/Normal/Bluish/User Mode
-------------------	---------------------------------

K Locker	Yes
----------	-----

OSD Language	18 Languages (English / Francais / Deutsch / Italiano / Espanol / Polish / Czech / Hungarian /Korean / Romanian / Netherlands / Russian / Swedish / Protuguese / Japanese / Chinese / S-Chinese / Arabic)
--------------	---

HDCP	1.4
------	-----

VESA Wall Mount	100x100 (mm)
-----------------	--------------

AMA	Yes
-----	-----

Eye Care

Flicker-free Technology	Yes
-------------------------	-----

Low Blue Light	Yes
----------------	-----

Brightness Intelligence (B.I.)	Yes
--------------------------------	-----

Connectivity

D-sub	D-sub x1
-------	----------

HDMI	HDMI (v1.4)x2
------	---------------

Power

Voltage Rating	100 - 240V
----------------	------------

Power Supply	Built-in
--------------	----------

Power Consumption (on mode.)	25W
------------------------------	-----

Power Consumption (based on Energy Star)	16W
--	-----

Dimension and Weight

Dimensions (HxWxD mm)	489.5*391.6*183
Net Weight (kg)	3.7Kg
Gross Weight (kg)	2.9Kg
Tilt (down/up)	-5° - 20°

Environmental Standards

Energy Star	7.0
EPEAT	Silver

Compliant Standards

TCO	7.0
-----	-----

Certification

Windows® Compatible	Yes
TUV Certificate	TUV Flicker-free, TUV LBL