

## Main Specifications

Screen Size	21.5
Resolution (max.)	1920x1080

## All Specifications

### Display

Screen Size	21.5
Panel Type	IPS
Backlight Technology	LED
Resolution (max.)	1920x1080
Brightness	250
Native Contrast(typ.)	1000:1
Viewing Angle (L/R;U/D) (CR $\geq$ 10)	178/178
Response Time	5ms (GtG)
Aspect Ratio	16:9
Display Colors	16.7 million colors
Color Gamut	72% NTSC
Display Area(mm)	476.06x267.79
PPI	102
DCR (Dynamic Contrast Ratio) (typ.)	20,000,000:1
Color Bit	8-bit

### Audio

Built-in Speaker	1Wx2
Headphone Jack	Yes
Audio Line In	Yes

## Monitor

Product Color	Black
Color Temperature	Reddish/Normal/Bluish/User Mode
HDCP	1.4
VESA Wall Mount	100x100 (mm)
AMA	Yes

## Eye Care

Flicker-free Technology	Yes
Low Blue Light	Yes
Brightness Intelligence (B.I.)	Yes

## Connectivity

D-sub	D-sub x1
HDMI	HDMI (v1.4)x2

## Power

Voltage Rating	100 - 240V
Power Supply	Built-in
Power Consumption (on mode.)	25W
Power Consumption (based on Energy Star)	16W

## Dimension and Weight

Dimensions (HxWxD mm)	489.5x391.6x183 mm
Net Weight (kg)	3.7 Kg
Gross Weight (kg)	2.9 Kg
Tilt (down/up)	-5° - 20°

## **Environmental Standards**

Energy Star	7.0
EPEAT	Silver

## **Compliant Standards**

TCO	7.0
-----	-----

## **Certification**

Windows® Compatible	Yes
---------------------	-----