

## Main Specifications

Screen size	27.9
Resolution (max.)	3840x2160

## All Specifications

### Display

Screen size	27.9
Panel Type	TN
Backlight Technology	LED backlight
Resolution (max.)	3840x2160
Brightness	300
Native Contrast (typ.)	1000:1
Viewing Angle (L/R;U/D) (CR>=10)	170/160
Response Time	1ms (GtG)
Refresh Rate	60Hz
Aspect Ratio	16:9
Display Colours	1.07 billion colors
Colour Gamut	72% NTSC
Display Area (mm)	620.9 x 341.3
PPI	158
DCR (Dynamic Contrast Ratio) (typ.)	12,000,000:1
Colour Bit	10 bit

### Audio

Built-in Speaker	2Wx2
Headphone Jack	Yes

## Monitor

Product Colour	Metallic grey
Colour Temperature	Reddish/Normal/Bluish/User mode
K Locker	Yes
OSD Language	18 Languages (English / Francais / Deutsch / Italiano / Espanol / Polish / Czech / Hungarian / Romanian / Nether-lands / Russian / Swedish / Portuguese / Japanese / Chinese / S-Chinese / Arabic/ Korean)
HDCP	2.2
VESA Wall Mount	Yes
AMA	Yes

## Eye Care

Flicker-free Technology	Yes
Low Blue Light	Yes
Brightness Intelligence Plus (B.I.+)	Yes

## Video Enjoyment

Smart focus	Yes
Super Resolution	Yes

## Gaming

FreeSync	Yes
----------	-----

## Connectivity

HDMI	HDMI (v2.0)x2
------	---------------

DisplayPort

DisplayPort (v1.4)x1

## Power

Voltage Rating

100 - 240V

Power Supply

Built-in

Power Consumption (on mode.)

<55W

## Dimension and Weight

Dimensions (HxWxD mm)

476.27x657.9x194.6

Net Weight (kg)

5.7

Gross Weight (kg)

7.2

Tilt (down/up)

-5° - 15°

## Certification

Mac-Compatible

Yes

Windows®-Compatible

Yes

TUV Certificate

TUV Flicker-free, TUV LBL