



## Description

Wherever flame retardants is important, this products is used for mechanical protection of cables and hoses. It is Halogen free.

## Application

For protecting cable looms before and after installation.

## Specifications

Material : LDPE - Low Density Polyethylene  
Service Temperature Range : -50°C to +50°C  
Oxygen Index : 35% -Test ISO 4589-2 (ASTM D2863). 0% Halogen Content Test IEC 60754-1

## Part Number Table

Description	Size OD (mm)	Wall Thickness (mm)	Part Number
Spiral Binding, LDPE, White, 50m	3	0.2	PP002671
Spiral Binding, LDPE, White, 50m	6	1.25	PP002672
Spiral Binding, LDPE, White, 25m	12	1.75	PP002673

**Important Notice** : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-POWER is the registered trademark of the Group. © Premier Farnell Limited 2016.