

Wall Plate Audio Amplifier with CSR Bluetooth v4.2 User Manual

FEATURES

- Bluetooth v4.2 with apt-X
- 24W class-D high quality power amplifier
- Compact size wall plate design
- Easy installation

SPECIFICATIONS

- Audio Inputs :Bluetooth Receiver or stereo audio line level
- Bluetooth Version: Bluetooth v4.2 compliant with apt-X
- Bluetooth Receive Distance:50 Meters (open space)
- Power Amplifier Type :Stereo Class-D
- Output power: 24W(rms) per channel (@ RL=4 ohm)
- THD+N :0.1 % (@ RL=4 ohm, f = 1 kHz)
- Minimum Load Resistance :4 ohm
- Includes Speaker Protection circuit.
- Power Source:24 VDC/3A
- 3 min link-lost timeout function.
Bluetooth automatically switch to pairing state if reconnecting fail.
- Audio priority: BT > Aux In


CONNECT AND OPERATE

STEP 1: Install the unit in wall and connect power and speaker cables

STEP 2: Turn on the rotary switch to power up

STEP 3: BT status LED quick blinking in open pairing mode, connect your BT devices to **Music-BT** and play

STEP 4: For Aux-In source, plug-in audio cable and play. The unit will automatically switch between BT and Aux-In



Setup Diagram