

RC1PG

Specifications and dimensions



- Green push button enclosed
- Momentary operation
- Plastic enclosure

Features	
Height	74mm
Width	68mm
Depth	51mm
Depth including head	73mm
Weight	0.16Kg
Colour	Grey lid on dark grey base
Enclosure construction	ABS plastic
Standard	EN 60947-5-1
Degree of protection	IP65
Operating temperature	-25°C to +70°C
Mechanical life	10 ⁶ operations
Cable capacity of terminals	2 x 1.5mm ²
Rated thermal current I _{th}	10A
Pushbutton reference	RP2-BA2
Contact block reference	RAS-BCBNO
Related products	
NO contact block (plastic enc)	RAS-BCBNO
NC contact block (plastic enc)	RAS-BCBNC

ⓘ ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Information provided in data sheets and/or specifications may vary from actual results in different applications and performance may vary over time. **All products must be installed according to manufacturers instructions.**

Europa House, Airport Way, Luton, Beds, LU2 9NH Tel: 01582 692 440 / Fax: 01582 692 450 e-mail: sales@europacomponents.com
website: <http://www.europacomponents.com>