

**ENER-J®**

Smart Home Living

# Bluetooth Fingerprint Lock

## FINGERPRINT & BLUETOOTH PADLOCK



SKU Code: SHA5260

EAN Code: 7061259203256

### Fingerprint and Bluetooth Padlock




#### Key Points

- With ENER-J's fingerprint unlock design you don't have to worry about losing your keys or forgetting password. Through Capacities Touch Sensor, our smart padlock can identify your fingerprint accurately. Supports up to 16 groups of fingerprints.
- We select ADC12 Aluminum Alloy and Type 303 Stainless Steel as material, which has excellent strength and will never rust. Great security performance will protect your cabinet and home against thieves.
- Using QR Code provided in package to download free APP (for Android and iOS), one can then enjoy convenient keyless design and share access with friends, family.
- Battery display of APP can remind you to charge it on time. Can be easily charged by USB cable (micro USB port on bottom). By one full charge, the built-in battery can keep standby for one month or 1000 times unlock.
- IP65 waterproof function can withstand ordinary wet environments and rainy weather. Perfect for outdoor and indoor use, such as suitcases, cabinets, bicycle, backpacks, school lockers, etc.


#### Features

- **Material:** ADC12 Aluminum Alloy + 304 Stainless Steel
- **BT Version:** 4.0
- **BT Working Frequency:** 2.4G
- **System Requirement for iOS/Android:** 4.3 and above
- **Battery:** built-in 1 \* 3.7V 130mAh 501225 polymer battery
- **Working Voltage:** 3.7V
- **Service Time:** about 1-month standby time
- **Unlock Times:** over 1000 continuous unlock times
- **Unlock Record:** 1000pcs
- **Fingerprint:** 16 groups
- **Charging Method:** Micro USB, 5V 130mA (USB cable is not included)
- **Waterproof Grade:** IP65
- **Work Environment:** Temperature: -25-80°C; Humidity: 5%-95%
- **Lock Size:** 7.8 \* 5 \* 2.3cm
- **Lock Weight:** 105g / 3.7oz
- **Package Size:** 12.1 \* 8.4 \* 3.5cm / 4.8 \* 3.3 \* 1.4in
- **Package Weight:** 160g / 5.6oz
- **Bluetooth parameters**
  - **Bluetooth chip:** TI-CC2541
  - **Working frequency band:** 2.4G
  - **Receive sensitivity:** -90dbm
  - **Transmit power:** -8.5dbm
  - **Secure encryption:** AES encryption
  - **Bluetooth version:** 4.0 BLE
  - Support 360° discrimination function
  - Support fingerprint stitching function





Specifications			
Surface treatment	Lock body	Surface dusting	
	Lock Beam	Stainless steel color (over 48 hours salt spray test)	
	Communication method	Bluetooth BLE	
Unlock mode	Bluetooth connection	Mobile phone APP or fingerprint unlock	
Supported equipment	iOS	Android 4.3 or above	
Unlock time	Within about 5 seconds after receiving the unlock command	Fingerprint entry	16 group
		Duration time	Standby for one month, continuously unlock more than 1000 times
Charging method	Rechargeable, 5V 130mA (Micro USB)	Waterproof rating	IP65
Working temperature (relative humidity)	-25~+80 degrees Celsius, 5%~95%	Bluetooth chip	TI-CC2541
Lock beam tensile force	Take 6 units to make a large SKY image in square		



**Emergency Charging**