



Quality Products. Service Excellence.

Liquid-Tight Cordgrips (Nickel Plated Brass) 1427BCG Series


IP68, UL Listed. PG & Metric

Features



- Liquid-tight cordgrip made from nickel plated brass
- Used where cable is entering or leaving an enclosure.
- Accepts a wide range of cable diameters due to large opening and NBR (nitrile rubber) seal.
- The strain relief elements tighten in a circular sequence on the sealing ring to give outstanding strain relief without twisting or damaging the cable.
- Use the cordgrip with the smallest maximum diameter that will fit your application (see table below).
- Locknut and EPDM o-ring included (as shown).
- Designed to meet NEMA Type 4, 4X, 6, 6P, 12 & 13 - Protection to IP68.
- UL listed.





PG Threads

Part Number	Material	Thread Size (D)	Wire Diameter		Outer Length (L)	Inner Thread Length (T)	Tool Size (mm)
			Min	Max			
1427BCGPG7	Nickel Plated Brass	PG7	3	4	19	5	14
1427BCGPG9	Nickel Plated Brass	PG9	4	8	21	6	17
1427BCGPG11	Nickel Plated Brass	PG11	5	10	22	6	20
1427BCGPG13	Nickel Plated Brass	PG13	6	12	23	7	22
1427BCGPG16	Nickel Plated Brass	PG16	10	14	24	7	24
1427BCGPG21	Nickel Plated Brass	PG21	13	18	24	7	30

Part Number	Material	Thread Size (D)	Wire Diameter		Outer Length (L)	Inner Thread Length (T)	Tool Size (mm)
			Min	Max			
1427BCGPG29	Nickel Plated Brass	PG29	18	25	31	8	40
1427BCGPG36	Nickel Plated Brass	PG36	22	32	37	8	50
1427BCGPG42	Nickel Plated Brass	PG42	32	38	37	9	57
1427BCGPG48	Nickel Plated Brass	PG48	37	44	38	10	64

Metric Threads

Part Number	Material	Thread Size (D)	Wire Diameter		Outer Length (L)	Inner Thread Length (T)	Tool Size (mm)
			Min	Max			
1427BCGM12	Nickel Plated Brass	M12x1.5	3	7	19	7	14
1427BCGM16	Nickel Plated Brass	M16x1.5	4	8	21	6	19
1427BCGM16L	Nickel Plated Brass	M16x1.5	5	10	22	6	20
1427BCGM20	Nickel Plated Brass	M20x1.5	6	12	23	6	22
1427BCGM20L	Nickel Plated Brass	M20x1.5	10	14	24	6	24
1427BCGM25	Nickel Plated Brass	M25x1.5	13	18	25	7	30
1427BCGM32	Nickel Plated Brass	M32x1.5	18	25	31	8	40
1427BCGM40	Nickel Plated Brass	M40x1.5	22	32	37	8	50
1427BCGM50	Nickel Plated Brass	M50x1.5	32	38	37	9	57
1427BCGM63	Nickel Plated Brass	M63x1.5	29	35	38	10	68

Data subject to change without notice

© 2019. Hammond Manufacturing Ltd. All rights reserved.