

TC15AH / TC30AH 100V 8" & 10" Round Reflex Horn Speakers



Rugged, weather resistant P.A. horn speakers manufactured with grey, epoxy coated aluminium. The horn has an integral 100V multi-tap transformer and power tapping switch which is easily selected from the rear of the unit using a screwdriver. Supplied with an adjustable U shaped mounting bracket.

- Aluminium speaker horn
- Grey epoxy coating
- Integrated multi-tap 100V transformer
- Tapping selector switch on rear
- Adjustable U shaped mounting bracket
- IP rating: IP66

	TC15AH	TC30AH
Type	Reflex - Round (8")	Reflex - Round (10")
Rated Input Power	15W	30W
Transformer Taps	1, 3, 5, 10, 15W	1, 3, 5, 10, 15, 30W
Input Impedance (100V)	670 Ω, 1k, 2k, 3.3k, 10kΩ	330 Ω, 670 Ω, 1k, 2k, 3.3k, 10kΩ
Pre-set Impedance (100V)	670 Ω	330 Ω
Frequency Response	280 Hz ~ 12.5 kHz	250 Hz ~ 16 kHz
SPL (1W/1m)	108 dB	109 dB
Coverage (at 1kHz)	80° conical	90° conical
IP Rating	IP66	IP66
Material	Horn flare: Aluminium	Horn flare: Aluminium
	Inner horn & rear cover: ABS	Inner horn & rear cover: ABS
Bracket	"U" shaped	"U" shaped

