

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0190540075](#)  
**Status:** **Active**  
**Description:** RING INSULKRIMP (B-218-38X)

**Documents:**

|  |  |
|--|--|
| <a href="#">Drawing (PDF)</a>                                | <a href="#">Product Specification PS-19902-013-001 (PDF)</a> |
| <a href="#">Product Specification PS-19902-009-001 (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a>         |
| <a href="#">Product Specification PS-19902-011-001 (PDF)</a> |  |

**Agency Certification**

|     |         |
|-----|---------|
| CSA | LR18689 |
| UL  | E32244  |

**General**

|                         |                          |
|-------------------------|--------------------------|
| Product Family          | Ring and Spade Terminals |
| Series                  | <a href="#">19054</a>    |
| Crimp Quality Equipment | Yes                      |
| UPC                     | 800753054370             |

**Physical**

|              |         |
|--------------|---------|
| Flammability | 94V-0   |
| Net Weight   | 1.410/g |

**Solder Process Data**


|                             |     |
|-----------------------------|-----|
| Lead-freeProcess Capability | N/A |
|-----------------------------|-----|

**Material Info**

|                    |           |
|--------------------|-----------|
| Engineering Number | B-218-38X |
|--------------------|-----------|

**Reference - Drawing Numbers**

|                       |   |
|-----------------------|---|
| Product Specification | PS-19902-009-001, PS-19902-011-001,<br>PS-19902-013-001 |
| Sales Drawing         | BCD20101  |



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
-ED/01/2018 (15  
January 2018)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[19054 Series](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

| Description   | Product #                 |
|---|---------------------------|
| PremiumGrade Hand<br>Crimp Tool                     | <a href="#">640010100</a> |
| Crimp Head for the<br>AT-200 Pneumatic<br>Hand Tool | <a href="#">640050100</a> |