


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0462355003](#)
Status: **Active**
Overview: Micro-Fit 3.0 Connector System Product Family
Description: Micro-Fit RMF High Mating Cycle, Reduced Mating Force, Crimp Terminal, Female, with 0.38µm Selective Gold (Au) over Nickel (Ni), 26-30 AWG, with Lubricant

Documents:

Drawing (PDF)	Packaging Specification PK-46235-001 (PDF)
Product Specification PS-46235-001-001 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification TS-46235-001-001 (PDF)	Product Literature (PDF)
Product Specification TS-46235-501-001 (PDF)	



General

Product Family	Crimp Terminals
Series	46235
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	90% increase in mating cycles (250 cycles) and up to 50% reduction in mating force, 90% increase in mating cycles (250 cycles) and up to 50% reduction in mating force
Crimp Quality Equipment Overview	Yes
Product Literature Order No	Micro-Fit 3.0 Connector System Product Family
Product Name	987650-5984
UPC	Micro-Fit RMF 883906382391

Physical

Durability (mating cycles max)	250
Gender	Female
Material - Metal	Copper-Zinc-Tin
Material - Plating Mating	Gold
Material - Plating Termination	Nickel
Net Weight	0.046/g
Packaging Type	Reel
Plating min - Mating	0.381µm
Plating min - Termination	1.270µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.27mm max.
Wire Size AWG	26, 28, 30
Wire Size mm ²	N/A

Electrical

Current - Maximum per Contact	5.0A
-------------------------------	------

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-46235-001
Product Specification	PS-46235-001-001, TS-46235-001-001, TS-46235-501-001
Sales Drawing	SD-46235-001

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -ED/88/2018 (15 January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[46235](#) Series

Mates With

[43031](#) Micro-Fit 3.0 Male Crimp Terminals

Use With

[43025](#) , [43645](#) Micro-Fit 3.0 Receptacle Housings, [44133](#) Micro-Fit BMI Panel Mount Receptacle Housings

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Extraction Tool	11030043
Hand Crimp Tool for Low Force Crimp Terminals	638192900
FineAdjust for Low Force Crimp	639001300

Terminal, 26-30
AWG Wire
T2 Terminator 639101300
Tooling Die for Crimp
Terminal, 26-30
AWG Wire

This document was generated on 03/11/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION