

13 Electricians' Pliers



13 01 160



- The ideal pliers for cable work
- For gripping and bending wire
- For cutting medium hard and hard wire
- Precision cutting edges additionally induction hardened, cutting edge hardness approx. 60 HRC
- With precision stripping holes
- For crimping end sleeves (ferrules)
- Vanadium steel, forged, oil-hardened in multiple steps






13 02 160



Product Number	UPC 8432210-		Pliers	Head	Handles	Ø Inch / Ø mm	Ø Inch / Ø mm	Stripping capacities in square inch in ² / mm ²	↔ Inch / mm	⚖ lbs
13 01 160	02497		black atramentized	polished	plastic coated	3/32 2.5	1/16 1.6	1/64 - 1/32 / 1/16 / 3/32 0.5 - 0.75 / 1.5 / 2.5	6 1/4 160	0,247
13 01 614	03968		black atramentized	polished	plastic coated	3/32 2.5	1/16 1.6		6 1/4 160	0,247
13 01 614 T BKA	03968		black atramentized	polished	plastic coated	3/32 2.5	1/16 1.6		6 1/4 160	0,247
13 02 160	11581		black atramentized	polished	with multi-component grips	3/32 2.5	1/16 1.6	1/64 - 1/32 / 1/16 / 3/32 0.5 - 0.75 / 1.5 / 2.5	6 1/4 160	0,306
13 02 614 T BKA			black atramentized	polished	with multi-component grips	3/32 2.5	1/16 1.6	1/64 - 1/32 / 1/16 / 3/32 0.5 - 0.75 / 1.5 / 2.5	6 1/4 160	0,317


technical change and errors excepted



Gripping



Cutting



Stripping



Crimping 0.5 to 2.5 mm² /
AWG 14 - AWG 20