

Statguard® Dissipative Neutral Floor Cleaner

Application Instructions



Made in the
United States of America



Figure 1. Statguard® Dissipative Neutral Floor Cleaner

Description

Statguard® Dissipative Neutral Floor Cleaner is formulated to clean floors treated with [Statguard® Dissipative Floor Finish](#) and [Statguard® Low-VOC Dissipative Floor Finish](#), as well as other dissipative or conductive floor tiles and polymer type floor finishes. It is formulated with dissipative agents that will rejuvenate and improve the static dissipative properties of the flooring surface that it is used with without leaving behind residue that can impede dissipation or conductive properties of the flooring material or finish.

Application

The Statguard® Dissipative Neutral Floor Cleaner is more aggressive than using a damp mop with a diluted finish and water and does reduce the gloss down as it cleans the surface. Heavy to moderate traffic floors can be cleaned once a week. Light traffic floors can be cleaned 2 to 3 times a month or as needed.

Testing a small area for compatibility if Statguard® Dissipative Neutral Floor Cleaner has not been used before is recommended.

EQUIPMENT NEEDED:

- Push broom
- Clean and untreated mop
- 2 dedicated buckets
(Clean bucket and rinse bucket)
- Statguard® Dissipative Neutral Floor Cleaner

1. Push broom the surface to be cleaned.
2. For damp mop, dilute Statguard® Dissipative Cleaner 10 to 1 (five (5) gallons of clean water to two (2) quarts of cleaner concentrate). For scrub use 15 to 1.
3. Thoroughly mix the cleaner solution before damp mop application. Use a clean, untreated mop to damp mop the area. Wring out excess fluid and do not flood a treated floor with water. For a scrubbing machine use 175 to 350 RPM with red pad.
4. Allow 30 to 60 minutes drying time before walking on the cleaned area.

Clean floors treated with Statguard® Floor Finish using Statguard® Cleaner. Do not damp mop with high alkaline or high residue cleaner. Using harsh detergents can damage a treated floor's static dissipative properties.

Physical Properties

% Solids	10%
pH	7.0
Color	Green
Ordor	Floral
Coverage	20,000 sq.ft./gal. of concentration
Freeze/Thaw Stability	Passes three cycles
Drying Time	30 - 60 min. @ 55% RH
Surface Resistivity	1 x 10 ⁶ to < 1 x 10 ⁹ ohms per ANSI/ESD STM7.1 and ESD TR53

Storage

Statguard® Dissipative Neutral Floor Cleaner does not have a set life span. The chemicals are not known to degrade over time when stored at the proper temperature conditions as stated in the Safety Data Sheet. We also recommend that the product be stored in its original container and be sealed when not in use.

RoHS, REACH, and Conflict Minerals Statement

See the Desco Industries RoHS, REACH, and Conflict Minerals Statement:

DescoIndustries.com/ROHS.aspx

Desco Industries Limited Warranty

See the Desco Industries Limited Warranty:

DescoIndustries.com/Warranty.aspx

Statguard® Dissipative Neutral Floor Cleaner is available from these Desco Industries brands:

DESCO

for service and support in North America

2.5 Gallons [10561](#)

5.0 Gallons [10566](#)

STATGUARD FLOORING

for service and support in North America

2.5 Gallons [46030](#)

5.0 Gallons [46031](#)

DESCO EUROPE

for service and support in United Kingdom and Europe

10 Litres [220522](#)

DESCO ASIA

for service and support in Asia

10 Liters [10561](#)

20 Liters [10566](#)