

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0193240015](#)  
**Status:** **Active**  
**Overview:** Metric Ring Terminals  
**Description:** Avikrimp Metric Ring Terminal for Stud Size 5/16" (M8), Insulated Barrel

**Documents:**

[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Drawing \(PDF\)](#)

**Agency Certification**

UL E32244

**General**

Product Family Ring and Spade Terminals  
 Series [19324](#)  
 Crimp Quality Equipment Yes  
 Mil-Spec N/A  
 Overview [Metric Ring Terminals](#)  
 Product Name Avikrimp  
 Type Ring  
 UPC 887191290157

**Physical**

Barrel Type Closed - Brazed  
 Flammability 94V-2  
 Insulation Nylon (PA)  
 Material - Metal Copper Alloy  
 Material - Plating Mating Tin  
 Net Weight 2.628/g  
 Packaging Type Bag  
 Stud Size 5/16" (M8)  
 Wire Size AWG N/A  
 Wire Size mm<sup>2</sup> 2.50-6.00

**Solder Process Data**

Lead-freeProcess Capability N/A

**Material Info**

Engineering Number C6-830-M8

**Reference - Drawing Numbers**

Sales Drawing SD-19324-001-001



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**China RoHS**

**REACH SVHC**

Not Contained Per  
 -ED/88/2018 (15  
 January 2019)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

**Search Parts in this Series**

[19324 Series](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
PremiumGrade Hand Crimp Tool	<a href="#">640010100</a>
Crimp Head for the AT-200 Pneumatic Hand Tool	<a href="#">640050100</a>

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**