

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0192040017](#)  
**Status:** **Active**  
**Overview:** [Splices](#)  
**Description:** Avikrimp 4 Way Splice for 14-16 AWG Wire

**Documents:**

[Drawing \(PDF\)](#) [Product Specification PS-19902-013-001 \(PDF\)](#)  
[Product Specification PS-19902-009-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-19902-011-001 \(PDF\)](#)

**General**

Product Family [Splices](#)  
Series [19204](#)  
Comments 4 Way Connector, 4 Way Connector  
Crimp Quality Equipment Yes  
Mil-Spec N/A  
Overview [Splices](#)  
Product Name 4 Way, Avikrimp  
UPC 800753051669

**Physical**

Barrel Type Closed  
Color - Resin Natural  
Insulation Nylon (PA)  
Material - Metal Copper  
Material - Plating Mating Tin  
Material - Plating Termination Tin  
Material - Resin Nylon  
Net Weight 5.372/g  
Packaging Type Bag  
Plating min - Mating 2.540µm  
Plating min - Termination 2.540µm  
Temperature Range - Operating -55° to +105°C  
Wire Insulation Diameter 4.32mm max.  
Wire Size AWG 14, 16  
Wire Size mm<sup>2</sup> 1.30-2.00

**Electrical**


Voltage - Maximum 600V

**Material Info**

Engineering Number B-5XC

**Reference - Drawing Numbers**

Product Specification PS-19902-009-001, PS-19902-011-001,  
PS-19902-013-001  
Sales Drawing SD-19204-002



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Contained Per -  
ED/30/2017 (7 July  
2017)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[19204 Series](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

**Description**

**Product #**

PremiumGrade HandCrimp Tool [640010100](#)  
Crimp Head for the AT-200 Pneumatic Hand Tool [640050100](#)