

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0857914020](#)
Status: **Active**
Overview: [Magnetic Jacks](#)
Description: PDJack Gigabit Single Port Magnetic Jack with Integrated POE+, Class 4

Documents:

[3D Model](#) [Packaging Specification PK-85759-001-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-85791-001-001 \(PDF\)](#)

General

Product Family	Modular Jacks/Plugs
Series	85791
Component Type	PCB Jack
Magnetic	Yes
Overview	Magnetic Jacks
Performance Category	5, 5e
Power over Ethernet (PoE)	PoE+
Product Name	Magnetic Jack, Modular Jack 8/8, PDJack, RJ45
UPC	887191157368

Physical

Boot Color	N/A
Color - Resin	Black
Durability (mating cycles max)	750
Inverted / Top Latch	Yes
Jack Height	13.87mm
Lightpipes/LEDs	None
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	PBT
Net Weight	11.097/g
Orientation	Right Angle (Side Entry)
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Panel Mount	Spring Tabs
Pitch - Mating Interface	1.02mm
Pitch - Termination Interface	2.03mm
Plating min - Mating	0.762µm
Port Configuration	1x1
Positions / Loaded Contacts	8/8
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	0° to +55°C
Termination Interface: Style	Through Hole
Waterproof / Dustproof	No
Wire/Cable Type	N/A

Electrical

Current - Maximum per Contact	1.0A
Grounding to PCB	Yes
Grounding to Panel	Yes
Shielded	Yes
Voltage - Maximum	60V AC



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 7(a),7(c)-I

REACH SVHC

Contained Per - ED/88/2018 (15 January 2019)

Lead

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[85791 Series](#)

Mates With

Plugs according to IEC 60603-7

Material Info

Reference - Drawing Numbers

Packaging Specification

PK-85759-001-001

Product Specification

PS-85791-001-001

Sales Drawing

857910020-000

This document was generated on 03/18/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION