

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0008700064**  
**Status:** **Active**  
**Overview:** KK® Interconnect System - Molex  
**Description:** KK Cat Ear Crimp Terminal 5159, 22-28 AWG, Reel, Brass, Tin (Sn) over Copper Plating

**Documents:**

<a href="#">3D Model</a>	<a href="#">Product Specification PS-5051-006-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Product Specification PS-5102-004-001 (PDF)</a>
<a href="#">Product Specification PS-5045-001 (PDF)</a>	<a href="#">Product Specification PS-5159-001 (PDF)</a>
<a href="#">Product Specification PS-5045-002 (PDF)</a>	<a href="#">Product Specification PS-5159-002-001 (PDF)</a>
<a href="#">Product Specification PS-5051-003 (PDF)</a>	<a href="#">Packaging Specification 51599200SPK-200 (PDF)</a>
<a href="#">Product Specification PS-5051-004 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**General**

Product Family	Crimp Terminals
Series	5159
Application	Signal, Wire-to-Board
Crimp Quality Equipment	Yes
Overview	<u>KK® Interconnect System - Molex</u>
Packaging Alternative	08700069 (Loose)
Product Name	Cat Ear, KK
UPC	800753534827

**Physical**


Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	40.000/mg
Packaging Type	Reel
Plating min - Mating	0.889µm
Plating min - Termination	0.889µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.20-1.70mm
Wire Size AWG	22, 24, 26, 28
Wire Size mm²	N/A

**Material Info**

Engineering Number 5159T

**Reference - Drawing Numbers**

Crimp Specification	CS-5159
Packaging Specification	51599200SPK-200
Product Specification	PS-5045-001, PS-5045-002, PS-5051-003, PS-5051-004, PS-5051-006-001, PS-5102-004-001, PS-5159-001, PS-5159-002-001
Sales Drawing	SD-5159X



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
-ED/88/2018 (15  
January 2019)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

5159 Series

**Use With**

2695 , 5051 , 6471 , 3071

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

**Description**

**Product #**

Extraction Tool [11030022](#)

Insertion Tool [638120000](#)

Mini-Mac Applicator [638882000](#)

for Insulation OD

1.09-1.57mm, 22-30

AWG Wire

Mini-Mac Applicator [638882100](#)

for Insulation OD

0.96-1.20mm, 22-30

AWG Wire

**Japan**

Description	Product #
Hand Extraction Tool	<u>11260059</u>

This document was generated on 03/14/2019

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**