

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0307001207](#)  
**Status:** **Active**  
**Overview:** H-DAC 64™ Dual-Row High Density Automotive Connectors  
**Description:** 2.54mm Pitch, 0.64mm Width H-DAC 64 High Density Automotive Connectors, Dual Row, Female Harness Assembly, 20 Circuits, Polarization Option 1, Gray

**Documents:**

<a href="#">3D Model</a>	<a href="#">Product Specification TS-30700-0001-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Application Specification AS-30700-000-001 (PDF)</a>
<a href="#">Product Specification PS-30700-0001-001 (PDF)</a>	<a href="#">Packaging Specification PK-30907-417 (PDF)</a>
<a href="#">Product Specification PS-30968-0001-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>



*Series image - Reference only*

**General**

Product Family	Crimp Housings
Series	30700
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	Polarization Option 1, Polarization Option 1
Overview	<a href="#">H-DAC 64™ Dual-Row High Density Automotive Connectors</a>
Product Name	H-DAC 64
UPC	822348516360

**Physical**

Circuits (maximum)	20
Color - Resin	Gray
Gender	Receptacle
Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	5.418/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +100°C

**Electrical**

Current - Maximum per Contact	7.0A
-------------------------------	------

**Solder Process Data**

Lead-freeProcess Capability	N/A
-----------------------------	-----

**Material Info**

**Reference - Drawing Numbers**

Application Specification	AS-30700-000-001
Packaging Specification	PK-30907-417
Product Specification	PS-30700-0001-001, PS-30968-0001-001, TS-30700-0001-001
Sales Drawing	SD-30700-120-001

**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
-ED/88/2018 (15  
January 2019)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Compliant

Not Contained

**Search Parts in this Series**

[30700 Series](#)

**Mates With**

H-DAC 64 Header [307004200](#) , [307004204](#) , [307005204](#) , [307005207](#) , Crimp Housing [30968](#)

**Use With**

Contact Molex for Terminal information.