

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0334721207](#)  
**Status:** **Active**  
**Overview:** [MX150 Sealed and Unsealed Connector System](#)  
**Description:** MX150 Sealed Female Connector, Dual Row, 12 Circuits, Polarization B, with Connector Position Assurance, Light Gray

**Documents:**

<a href="#">3D Model</a>	<a href="#">Application Specification AS-33611-001-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification PK-31300-903-001 (PDF)</a>
<a href="#">Product Specification PS-33472-000-001 (PDF)</a>	<a href="#">Packaging Specification PK-33472-001-001 (PDF)</a>
<a href="#">Application Specification AS-33472-100-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**General**

Product Family	Crimp Housings
Series	<a href="#">33472</a>
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	with Connector Position Assurance (CPA), with Connector Position Assurance (CPA)
More Detailed Tech Information	<a href="http://uscar.org/guest/teams/10/Electrical-Wiring-Component-Applications">http://uscar.org/guest/teams/10/Electrical-Wiring-Component-Applications</a> -Partnership
Overview	<a href="#">MX150 Sealed and Unsealed Connector System</a>
Polarization	B
Product Name	MX150
UPC	756054677490

**Physical**

Circuits (maximum)	12
Color - Resin	Gray (Light), Natural
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Modified Polystyrene Alloy
Net Weight	15.705/g
Number of Rows	2
Packaging Type	Individual Cell
Panel Mount	No
Pitch - Mating Interface	3.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C

**Solder Process Data**

Lead-freeProcess Capability	N/A
-----------------------------	-----

**Material Info**

**Reference - Drawing Numbers**

Application Specification	AS-33472-100-001, AS-33611-001-001
Packaging Specification	PK-31300-903-001, PK-33472-001-001
Product Specification	PS-33472-000-001
Sales Drawing	SD-33472-0001-001, SD-33472-0002-002



*Series image - Reference only*

**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
-ED/88/2018 (15  
January 2019)

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Not Relevant

Compliant

Not Contained

**Search Parts in this Series**

[33472](#) Series

**Mates With**

MX150 Male Sealed Connector [33482](#)  
<br>MX150 Male Bulkhead Twist-Lock  
Sealed Connector [348406420](#)

**Use With**

MX150 Female Terminal [33012](#) , [33001](#)  
<br>MX150 Cavity Plug Sealed [343450001](#)  
<br>MX150 Backshell [349511210](#) ,  
[349501220](#)