

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0345760703](#)
Status: **Active**
Overview: [MX123 Sealed Connection System](#)
Description: 2.54mm Pitch, MX123 Female Receptacle Housing, Keying Option G, Wire Dress Option 0, 56 Circuits, Blue TPA

Documents:

3D Model	Product Specification TS-34566-1546-001 (PDF)
Drawing (PDF)	Application Specification AS-34566-001-001 (PDF)
Product Specification PS-34566-0000-001 (PDF)	Packaging Specification PK-31300-019-001 (PDF)
Product Specification TS-34566-002-001 (PDF)	RoHS Certificate of Compliance (PDF)



General

Product Family	Crimp Housings
Series	34576
Application	Power, Wire-to-Board
Comments	See Sales Drawing for number of Open Circuits, See Sales Drawing for number of Open Circuits
Overview	MX123 Sealed Connection System
Product Name	MX123
UPC	822348356713

Physical

Circuits (maximum)	56
Circuits Detail	56
Color - Resin	Blue
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	41.804/g
Number of Rows	4
Packaging Type	Tray
Panel Mount	No
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C

Electrical

Current - Maximum per Contact	11.0A, 25.0A
-------------------------------	--------------

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Application Specification	AS-34566-001-001
Packaging Specification	PK-31300-019-001
Product Specification	PS-34566-0000-001, TS-34566-002-001, TS-34566-1546-001
Sales Drawing	12642694-001, 345760001-SD-000, SD-34576-0001-001, SD-34576-001-000

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per

-ED/88/2018 (15

January 2019)

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Not Relevant

Compliant

Not Contained

Search Parts in this Series

[34576 Series](#)

Mates With

MX123 Header [31386](#) , [31387](#)

Use With

MX64 Female Terminals [33467](#) (AWG, Gold)
MX64 Female Terminals [34736](#) (AWG, Silver)
MX64 Female Terminals [34736](#) (ISO, Silver)

This document was generated on 03/20/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION