

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1731120050](#)
Status: **Active**
Description: FCT Coaxial Contact, Male, Straight, Crimp Cable Termination, 50 Ohms, 1.30µm Gold Plating, for RG-174U, RG-188AU, or RG-316U Cable

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	D-Sub Products
Series	173112
Brochure Order No	987651-9941
Cable Attachment	Crimp
Contact Type	Coaxial Contact
Exclude SD Check	Yes
Impedance	50Ω
Product Category	Special Contacts
Product Name	FCT Products
UPC	889056322911
Wire/Cable Type	RG-174U, RG-188AU, RG-316U

Physical


Durability (mating cycles max)	200
Gender	Male
Material - Contact	Copper Alloy
Material - Plating Mating	Gold
Orientation	Straight
Packaging Type	Bag
Temperature Range - Operating	-55° to +135°C

Electrical

Current - Maximum per Contact	2.0A
-------------------------------	------

Material Info

Engineering Number	FMS001P102
--------------------	------------



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[173112 Series](#)

Use With

FCT Mixed Layout