

**Specifications:**

Impedance (Ω)	50 ± 15% at 1000 Hz at 1.0 V
Rated Power (W)	0.6
Max Power (W)	1.0
Resonance Freq Fo (Hz)	500 ± 15% at 1.0 V
Frequency Range (Hz)	Fo ~ 10000
Output S.P.L. (dB)	96 ± 3 at .6w/1m 0.8k, 1.0k, 1.2k, 1.5kHz 78 ± 3 at 1w/1m 0.8k, 1.0k, 1.2k, 1.5kHz
Frame Material	Metal
Operating Temp	-40 to 85°C
Weight (g)	3.6
Options	For other options contact factory

**Dimensions: ±0.3** (units: mm)

**ROHS Compliant**

