

**Specifications:**

Impedance (Ω)	8 ± 15% at 1000 Hz at 1.0 V
Rated Power (W)	0.1
Max Power (W)	0.2
Resonance Freq Fo (Hz)	460 ± 20% at 1.0 V
Frequency Range (Hz)	Fo ~ 5000
Output S.P.L. (dB)	88 ± 3 at .1w/.1m 1.0k, 1.2k, 1.5k, 2.0kHz 78 ± 3 at 1w/1m 1.0k, 1.2k, 1.5k, 2.0kHz
Frame Material	ABS UL-94 1/16" HB High Heat (Black)
Operating Temp	-20 to 55°C
Weight (g)	4.5
Options	For other options contact factory

**Dimensions: ±0.3** (units: mm)

**ROHS Compliant**

