

Specifications:

Impedance (Ω)	$8 \pm 15\%$ at 2000 Hz at 1.0 V
Rated Power (W)	1.0
Max Power (W)	1.5
Resonance Freq F_o (Hz)	$500 \pm 20\%$ at 1.0 V
Frequency Range (Hz)	$F_o \sim 10000$
Output S.P.L. (dB)	87 ± 3 at 1w/.1m 0.8k, 1.0k, 1.2k, 1.5kHZ 67 ± 3 at 1w/1m 0.8k, 1.0k, 1.2k, 1.5kHZ
Frame Material	Metal
Operating/Storage Temp	-20 to 60°C / -30 to 70°C
Weight (g)	9.7
Options	For other options contact factory

Dimensions: ± 0.2 (units: mm)

ROHS Compliant

