

RPT184520 | 18V Cordless Pole Hedge Trimmer, 45cm Blade (1x2.0Ah)



- Powerful 18V motor easily cuts through hedges and branches.
- 45cm diamond ground blades for clean cutting.
- Capable of cutting large branches with 18mm blade gap.
- 115° articulating cutting head with 4 positions for versatile trimming.
- Removable extension shaft for full length of 2.9m for extended reach tasks.

	RPT184520
Battery pack capacity (Ah)	2.0
Battery type	Li-ion
Blade length [cm]	45
Blade speed (rpm)	1350
Blade type	Diamond ground
Charger included?	Yes
Charging time	60
Max. cutting capacity (mm)	18
No. of batteries supplied	1
Oscillation angle left/ right (°)	115
Power	18V
Sound Power [dB Lwa]	92.8
Supplied in	Recyclable Carton
Vibration level [m/s ²]	1.3
Vibration uncertainty [m/s ²]	1.5
Weight [without battery] [Kg]	4.2
Weight with battery pack (kg)	4.6