

## OBL18JB | 18V Cordless Jet Blower

- High-efficiency jet fan design provides maximum performance.
- Variable speed control for ultimate versatility.
- Built-in debris scraper to loosen stubborn dirt and leaves.
- Overmould handle for comfort during extended use.



	OBL18JB
Air volume (m <sup>3</sup> per minute)	7.9
Airflow speed (km/h)	160
Battery type	Li-ion
Charger included?	No
No. of batteries supplied	0
Power	18 V
Sound Power [dB Lwa]	98.4
Supplied in	Recyclable Carton
Vibration level [m/s <sup>2</sup> ]	1.6
Vibration uncertainty [m/s <sup>2</sup> ]	1.5
Weight [without battery] [Kg]	2.1
Weight with battery pack (kg)	2.5