

RHT4550 | 450W Electric Hedge Trimmer, 50cm Blade, 20mm Cut



- Powerful yet lightweight 450W motor.
- Dual-action, diamond-ground blades for clean and precise cuts.
- 50cm blade cuts branches up to 20mm in diameter.
- Wrap-around front handle and overmould for increased user comfort.
- Compatible with HedgeSweep™ for a hassle-free way to clean clippings.

	RHT4550
Blade length [cm]	50
Blade speed (rpm)	1600
Blade type	Diamond ground
Max. cutting capacity (mm)	20
Power	450W
Sound Power [dB Lwa]	96.6
Supplied in	Recyclable Carton
T blade protector	No
Vibration level [m/s ²]	3.6
Vibration uncertainty [m/s ²]	1.5
Weight (kg)	2.9