

## R18PD31-213S | 18V Cordless Percussion Drill (2x1.3Ah)



- Cordless percussion drill ideal for drilling in wood or metal, driving screws or even drilling in masonry thanks to the hammer function.
- 13mm ratcheting chuck for improved bit gripping strength and durability.
- 2 gears to control the max speed to match different materials and applications.
- 24 torque settings help to drive screws flush every time.
- LED lights up your work area for better visibility.

	R18PD31-213S
Battery pack capacity (Ah)	2.0
Battery type	Li-ion
Charger included?	Yes
Charging time	90
Chuck capacity (mm)	13
Chuck Material	Metal
Max drilling steel (mm)	13
Max. drilling masonry (mm)	13
Max. drilling wood (mm)	38
Max. percussion rate (bpm)	6500 / 23400
Max. torque (Nm)	50
No load speed (rpm)	0-500 / 0-1800
No. of batteries supplied	2
Power	18V
Sound power level [dB(A)]	96.6
Supplied in	Tool bag
Torque settings	24
Weight [without battery] [Kg]	1.3
Weight with battery pack (kg)	1.7