

## R18AG7-0 | 18V Cordless Brushless Angle Grinder



- Powerful Brushless 125mm grinder ideal for a variety of cutting and grinding applications.
- Brushless motor eliminates friction to provide the power to cut, grind or even work with masonry.
- Intelligent electronics constantly regulate the motor to maximum runtime.
- Electronic anti-kickback technology shuts the tool down when a jam is detected improving user safety.
- 3 position handle for better control when grinding or cutting.
- Tool-less wheel guard and nut for easy accessory fitting.

	R18AG7-0
Bore size (mm)	22
Charger included?	No
Disc diameter (mm)	125
No load speed (rpm)	11000
No. of batteries supplied	0
Power	18V
Sound power level [dB(A)]	91.0
Sound power level uncertainty [dB(A)]	3.0
Sound pressure level (dB(A))	80.0
Sound pressure level uncertainty [dB(A)]	3.0
Spindle size	M14
Supplied in	Recyclable Carton
Vibration grinding [m/s <sup>2</sup> ]	3.9
Vibration grinding uncertainty [m/s <sup>2</sup> ]	1.5
Weight [without battery] [Kg]	2.2
Weight with battery pack (kg)	2.6