

R18MT3-0 | 18V Cordless Multi Tool



- A versatile multi purpose tool that cuts drywall, metal, wood, plastic, composite and many other materials; it also sands the finest details.
- Plunge cuts into any material quickly and easily or cut flush, right up to a surface without damaging it.
- Quick change attachments for hassle free transition between sanding and cutting.
- 6 position variable speed wheel for ultimate control across a range of applications.
- The universal accessory adaptor included makes this tool compatible with any brand of accessories.
- LED lights up your work area for better visibility.

	R18MT3-0
Charger included?	No
No. of batteries supplied	0
Oscillation angle	3<special {" id="5"/>
Oscillation rate (opm)	10000-20000
Power	18V
Sound power level [dB(A)]	101.5
Sound power level uncertainty [dB(A)]	3.0
Sound pressure level (dB(A))	90.5
Sound pressure level uncertainty [dB(A)]	3.0
Supplied in	Recyclable Carton
Vibration sanding (m/s ²)	4.2
Vibration sanding uncertainty [m/s ²]	1.5
Weight [without battery] [Kg]	0.85
Weight with battery pack (kg)	1.22