

---

**Model: OAHD-D4-1080P**



**OAHD 1080P AHD 4 Camera Hybrid 5 in 1 DVR**

---

Model: OAHD-D4-1080P	
Operating System	Embedded LINUX
Video Input	4 Channel BNC
Audio Input	1 Channel RCA
Audio Output	1 Channel RCA
IP Camera Support	Up to 4 (Disable BNC Channels)
Video Output	1 x HDMI, 1 x VGA, 1 x BNC
Display Split	1/4
Resolution	1080P/720P/960H
Video Compression	H264
Record Rate (Main Stream)	1080P/720P/960H - 25fps
Recording Mode	Continuous/Manual/Motion Detection
IP Recording Bandwidth (Min-Max)	512Kbps - 8Mbps
Sync Playback	4 Channel
Backup Mode	Network/USB
Ethernet	RJ45 10M/100M
Network Type	Lan, DHCP, DDNS, UDP, PPPoE, NTP
Network Monitoring	Web browsers, CMS, Android & iPhone app (N_Eye)
Wifi Connection	No
3G Connection	No
Internal Hard Drive	1 SATA HDD, Up to 8TB
Alarm Input	No

Alarm Output	No
PTZ Control	RS485
USB Interface	2 (Mouse/Backup/Upgrade)
Power Supply	DC12V/2A
Dimensions (WxHxD)	253x40x215

---