


**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0334670024](#)  
**Status:** **Active**  
**Overview:** MX64 Sealed Connectors  
**Description:** 2.54mm Pitch MX64 Terminal, Gold (Au) Plating, 0.50-0.75mm2 Wire, Right Reel Payoff, Also used with MX123 Female Receptacle Housing

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification PK-31300-516 (PDF)</a>
<a href="#">Product Specification PS-33468-001-001 (PDF)</a>	<a href="#">Packaging Specification PK-31302-480 (PDF)</a>
<a href="#">Application Specification AS-33468-002-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Packaging Specification PK-30907-759 (PDF)</a>	



*Series image - Reference only*

**General**

Product Family	Crimp Terminals
Series	<a href="#">33467</a>
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	Right Reel Payoff   For automatic and semi-automatic crimping, use Left Reel Payoff terminals. See Sales Drawing for Left Reel Payoff Part Numbers., Right Reel Payoff   For automatic and semi-automatic crimping, use Left Reel Payoff terminals. See Sales Drawing for Left Reel Payoff Part Numbers.
Crimp Quality Equipment Overview	Yes
Product Name	<a href="#">MX64 Sealed Connectors</a>
UPC	MX123, MX64 884982720664

**Physical**

Gender	Female
Material - Metal	Copper
Material - Plating Mating	Gold
Net Weight	0.222/g
Packaging Type	Reel
Plating min - Mating	0.762µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.50-2.06mm
Wire Size AWG	N/A
Wire Size mm²	0.50-0.75

**Material Info**

**Reference - Drawing Numbers**

Application Specification	AS-33468-002-001
Packaging Specification	PK-30907-759, PK-31300-516, PK-31302-480
Product Specification	PS-33468-001-001
Sales Drawing	SD-33468-002-001

**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -ED/88/2018 (15 January 2019)

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Not Relevant

Compliant

Not Contained

**Search Parts in this Series**

[33467 Series](#)

**Use With**

MX64 Sealed Single Row Crimp Housing 31403 , MX123 Female Receptacle Housing 34566 , 34576

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

**Description**

**Product #**

Hand Tool for MX64 ISO Terminal	<a href="#">638258400</a>
---------------------------------	---------------------------