

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0524652471](#)
Status: **Active**
Overview: SlimStack™ 0.35mm pitch Board-to-Board Connectors
Description: SlimStack Board-to-Board Connector, 0.80mm Pitch, Floating Series, Rigid Type Receptacle, 4.50 to 7.00mm Mated Height, 24 Circuits, without Boss

Documents:

3D Model	Packaging Specification SPK-52465-002-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-52465-010-001 (PDF)	Product Literature (PDF)
Product Specification PS-52465-014-001 (PDF)	Product Literature (PDF)
Product Specification PS-52465-015-001 (PDF)	

General


Product Family	PCB Receptacles
Series	52465
Application	Board-to-Board, Signal
Datasheet Order No	987651-8814, 987651-8815_ZH, 987651-8817_DE, 987651-8818_JA, 987651-8819_KO, 987651-8820_ES
Overview	SlimStack™ 0.35mm pitch Board-to-Board Connectors
Product Guide Order No	987651-8281
Product Literature Order No	987652-0196, Reference Guide#
Product Name	SlimStack
Series Name	0.80 Floating
UPC	822348142996

Physical

Circuits (Loaded)	24
Circuits (maximum)	24
Color - Resin	Natural
Durability (mating cycles max)	30
Glow-Wire Capable	No
Mated Height	4.50mm, 5.65mm, 6.00mm, 7.00mm
Mated Width	4.70mm, 5.10mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	246.800/mg
Number of Rows	2
Orientation	Vertical
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	0.80mm
Plating min - Mating	1.016µm
Plating min - Termination	1.016µm
Polarized to PCB	No
Surface Mount Compatible (SMC)	N/A
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Surface Mount

Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	50V



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[52465 Series](#)

Mates With

[53364](#) , [53353](#) , [53307](#) , [53309](#)

Material Info

Reference - Drawing Numbers

Packaging Specification

Product Specification

Sales Drawing

SPK-52465-002-001

PS-52465-010-001, PS-52465-014-001,

PS-52465-015-001

SD-52465-028, SD-52465-029

This document was generated on 04/02/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION