



22" Full HD LED TV with Freeview T2 HD, Satellite Tuner and DVD Player

- 22" Full HD widescreen LED TV
- Freeview T2 HD
- Built-in DVD Player
- USB – record digital TV and play media files from other devices
- HDMI input for your external devices and consoles
- Can be wall mounted (100mm x 100mm bracket not included)

	EAN	5060062268461
General Feature	Model No.	C22230FT2S2
	Panel(60Hz/120Hz/3D)	T215HUNO1
	Screen Size	21.5 inch LED Panel(Approx. 55cm)
	Max. Resolution	1920 x 1080 Full HD
	Contrast Ratio (Typical)	3000:1
	Brightness(TYP cd/m2)	180
	Viewing Angle (L/R/U/D)	89/89/89/89(CR≥10)
	Cabinet Colour	Piano Black
	Wall Mounting (Screw Size)	100 x 100mm(M4 x 8)

Reception	TV System	ATV: PAL BG/DK/1 SECAM BG/DK/L/L' DTV: DVB-S2, DVB-T & DVB-C&DVBT2, MPEG 2,MP@ML, MPEG 4
	TV Band	ATV 49MHz - 863MHz DTV VHF (174MHz-- 230MHz) UHF (474MHz-- 862MHz)
	5V from Antenna	N/A
	Number of channel for storing	100 Analog / 400 Digital

Sound	Bass	YES
	Treble	YES
	Balance	YES
	Sound Mode	Standard / Music /Movie / Sports /User
	Stereo System	NICAM/A2
	Audio Output	2 x 3W
	Speaker Frequency range	150-20K Hz
	Speaker Distortion	<=7% Max
	Speaker Impedance	4ohm

Connectors Jack	RF Antenna	1
	HDMI	YES x 1
	CVBS	YES x 1
	PC In	YES x 1
	Audio In	PC audio x 1 (3.5 φ Mini Jack) CVBS Audio x1 (Shared with Ypbpr)
	Scart	N/A
	YPbPr	YES x 1(3.5 φ Mini Jack)
	Digital Audio out	YES x 1
	Earphone Out	YES x 1
	USB on TV	YES x 1
	CI	YES x 1
	RCA	N/A
Satellite Input	YES	

DVD	DVD Loader	FORYOU
	DVD Solution	MTK-MTK1389
	DVD/DVD-R/DVD+R/DVD-RW/DVD+RW/ CD/MP3/JPEG playback	YES
	DVD Reverse Play	YES
	Skip Forward/Reverse	YES
	DVD Multi-Speed Scan/Slow	YES
	Slot-Load Type Vertical Play DVD Mechanism	YES
	DIV X	N/A

Other Features	APS	ATV, DVBT, DVBC storage in capture order
	OSD Language	English, Deutsch, Norge, Dansk, Svenska, Francais, Espanol, Portugese, Italian.
	EPG (Electronic Program Guide)	7 days
	Automatic Tuning	YES
	Sleep Timer	YES (240min)
	Color Temperature Adjustment	YES
	Picture Mode	Standard / Dynamic / Mild / User
	Home Mode	YES
Hotel Mode	YES	

Power	Power Supply	DC12V-3A /AC 100V-240V~ 50Hz/60Hz
	Operation Power Consumption	21W
	KWh/annum	31kWh
	Max power Consumption	36W
	Standby Power Consumption	<0.5W
	Energy Efficiency Class	A

Accessories	QSG	YES X 1
	Remote Control	YES x 1
	Adapter	YES x 1
	Warranty	YES x 1
	Battery	1.5V (AAA) x2

Dimension	Unit Dimension With Stand (W x D x H mm)	504 x 160 x 342
	Unit Dimension Without Stand (W x D x H mm)	504 x 79 x 306
	Weight of unit(kg)	2.55