



Powering Business Worldwide

pe.eaton.com

NEMA Freedom Series Non-Reversing Contactor

CN15DN3AB

UPC:782113973524

Dimensions:

- **Height:** 5.05 IN
- **Length:** 4.44 IN
- **Width:** 2.56 IN

Notes:Common Control

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Amperage Rating:** 27A
- **Max Hp Rating:** 2 hp at 115V, 3 hp at 230V, 7-1/2 hp at 208,240V, 10 hp at 480,600V
- **Number Of Poles:** Three-pole
- **Phase:** Single-phase, three-phase
- **Size:** 1

Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [CN15DN3_B 2D Drawing Xchange](#)
- [CN15DN3_B AutoCAD 2D Footprint](#)
- [CN15DN3_B AutoCAD 2D Footprint \(mm\)](#)
- [CN15DN3_B 2D PDF](#)
- [CN15DN3_B 3D Inventor](#)
- [CN15DN3_B 3D Model Xchange](#)
- [Quick Selector - NEMA Contactors](#)

Certifications:

- CSA Certified
- UL Listed



Product compliance: No Data

© 2016 Eaton. All rights reserved.