



msi

GRAPHICS CARD GEFORCE® GTX 1050 Ti 4GT OC



SPECIFICATION

Model Name	GeForce® GTX 1050 Ti 4GT OC
Graphics Processing Unit	NVIDIA® GeForce® GTX 1050 Ti
Interface	PCI Express x16 3.0
Core Name	GP107-400
Cores	768 Units
Core Clocks	1455 MHz / 1341 MHz
Memory Speed	7008 MHz
Memory	4GB GDDR5 (128-bit)
Output	DisplayPort (Version 1.4) / HDMI 2.0b / DL-DVI-D
HDCP Support	2.2
Power consumption	75 W
Recommended PSU	300 W
Card Dimension(mm)	215 x 112 x 38 mm
Weight (Card / Package)	444 g / 794 g
Afterburner OC	Y
DirectX Version Support	12
OpenGL Version Support	4.5
Maximum Displays	3
G-SYNC™ technology	Y
Adaptive Vertical Sync	Y
Digital Maximum Resolution	7680 x 4320

CONNECTIONS



1. DisplayPort
2. HDMI
3. DVI-D

FEATURE



DUAL FAN THERMAL DESIGN

Dual fans covers more area of heatsink to take heat away more efficiently.



Military Class 4 Components

Using only the highest quality components means you get reliable and stable in-game performance.



MSI Afterburner

The ultimate overclocking software with advanced control options and real-time hardware monitor.



OC PERFORMANCE

MSI OC graphics cards are equipped with higher clock speeds out of the box for increased performance.



NVIDIA G-SYNC™

Gives you more of what you want in a gaming experience. Incredibly smooth, tear-free gameplay at refresh rates up to 240 Hz.

PASCAL PERFORMANCE

Pascal-powered graphics cards give you superior performance and power efficiency to deliver the best gaming experiences.

GEFORCE GTX 1050 Ti