



SLEEK DESIGN.
POWERFUL PERFORMANCE.

Lenovo V145-15" LAPTOP



Lenovo[™]

Lenovo V145-15" LAPTOP

EVERYDAY BUSINESS MADE BETTER

Powered by up to AMD A9 Processors coupled with Windows 10 OS, the Lenovo V145-15" enables effortless productivity. The sleek design, convenient keyboard, and one-piece touchpad offer a seamless experience to mobile users. With the full-HD* display and Dolby® Audio™ certified stereo speakers, you can experience superior audiovisual clarity, no matter where work takes you.



Amplified Performance: with up to 8GB DDR4 memory and optional AMD Radeon™ 530 graphics with 2GB GDDR5 VRAM, this laptop can multitask with ease.



Versatile Storage: with the optional dual-drive storage, experience the responsiveness of a solid state drive (SSD) and the extra capacity of a hard disk drive (HDD).



Hassle-free Connectivity: a wide range of ports such as USB 3.0, HDMI, RJ45 along with the 4-in-1 card reader makes it easy for you to connect multiple peripherals for increased productivity.



Maximum Comfort: the 15" full-HD* anti-glare display minimizes eye fatigue, while the full-sized ergonomic keyboard with number pad and one-piece touchpad add to higher user comfort. The gapless keyboard ensures there is no dust build-up.



Superior Sound: with the Dolby® Audio™ certified stereo speakers, you can enjoy exceptional sound clarity.

ITDM Benefits

- **Productive:** robust performance with multiple ports and a rich user experience for enhanced efficiency.
- **Secure:** the integrated firmware TPM encrypts sensitive data and passwords, while the Kensington® lock slot physically protects your device from theft by securing it to an immovable object.
- **Reliable:** tested for optimum reliability and durability to perform smoothly.

*Optional





ACCESSORIES



Lenovo 400 Wireless Mouse

GY50R91293 (WW)

Comfortable and functional in either hand, this lightweight mouse offers exceptional quality with a modern wireless solution. Fast and accurate, it also provides a high precision of 1200dpi resolution.



Lenovo 500 Extra-bass In-ear headphone

GXD0J36366 Dark Gray (WW)

This in-ear headphone delivers exceptional sound clarity, creating a rich audio experience. A comfortable fit, tangle-free cord, and a hidden noise-canceling microphone make conference calls easier.



Lenovo 15.6" Laptop Casual Backpack

GX40Q17225 Black-ROW

Modern, durable, and stylish, this backpack with its conveniently placed compartments and pockets is perfect when on-the-go. Water-repellent fabric and a clean, streamlined design create a case that is ideally suited for everyday use.

Lenovo V145-15" Laptop

PERFORMANCE

Processor

AMD A9-9425
AMD A6-9225
AMD A4-9125

Memory

Up to 8GB DDR4

Storage

Up to 1TB 5400rpm HDD
Optional dual drive*
Up to 256GB SATA SSD

Optical Drive

Optional DVD+/-RW

OS

Windows® 10 Pro
Windows® 10 Home

Graphics

AMD Integrated graphics
AMD Radeon™ 530 2GB GDDR5 VRAM (optional)

Camera

0.3M or 720p with single mic

Audio

Stereo speakers with Dolby® Audio™

Battery

30Whr up to 5 hours**

* HDD in ODD bay

** Based on testing with MobileMark 2014. Battery life varies significantly with settings, usage, and other factors.

DESIGN

Display

15" FHD (1920 x 1080 pixels) with anti-glare
15" HD (1366 x 768 pixels) with anti-glare

Security

Kensington® lock slot

Dimensions (W x D x H)

mm: 376 x 253 x 22.7
Inches: 14.7 x 9.9 x 0.89

Weight

Starting at 2.1kg/4.62 lbs. (with battery)

Color

Black

Keyboard and Touchpad

Full-sized keyboard with number pad
One-piece touchpad

CONNECTIVITY

Input/Output Ports

2 x USB 3.0
HDMI
4-in-1 card reader (SD, SDHC, SDXC, MMC)
RJ45
Audio combo jack

LAN

1000M

WLAN

1 x 1 AC
Bluetooth® 4.1

RECOMMENDED SERVICES

Lenovo™ offers a comprehensive portfolio of services to support and protect your V145 laptop investment—so you can focus on your business, not your IT.

Warranty Extensions¹

This fixed-term, fixed-cost service helps accurately budget for PC expenses and protect your investment.

Warranty Upgrade to Onsite Service^{1,2}

Maximizes PC uptime and productivity by providing convenient, fast repair service at your place.

Accidental Damage Protection^{1,2}

Coverage for non-warranted damage incurred under normal operating conditions, such as spills, drops or damage to the integrated screen.

Lenovo Premier Support^{1,2}

Dedicated access to advanced troubleshooting and end-to-end case management.

Premium Support³

One-stop solution for non-warranty challenges with network, security and software setup, performance tune-up and more.

¹ Up to 3 years total duration

² May not be available in all countries

³ Available in Austria, Germany, Ireland, Switzerland and UK



© 2018 Lenovo. All rights reserved. These products are available while supplies last. Prices shown are subject to change without notice. For any questions concerning price, please contact your Lenovo Account Executive. Lenovo is not responsible for photographic or typographic errors. Warranty: For a copy of applicable warranties, write to: Warranty Information, 500 Park Offices Drive, RTP, NC 27709, Attn: Dept. ZPYA/B600. Lenovo makes no representation or warranty regarding third-party products or services. Trademarks: Lenovo, the Lenovo logo, Rescue and Recovery, ThinkPad, ThinkCentre, ThinkStation, ThinkVantage, and ThinkVision are trademarks or registered trademarks of Lenovo. Microsoft, Windows, and Vista are registered trademarks of Microsoft Corporation. AMD, the AMD Arrow logo, and combinations thereof are trademarks of Advanced Micro Devices, Inc. in the United States and/or other jurisdictions. Other company, product, and service names may be trademarks or service marks of others.

The image shows the Lenovo logo, which is the word 'Lenovo' in a white, sans-serif font, oriented vertically on a blue rectangular background.