



NTE Solder Wick



NTE Solder Wick is made from fine copper wire woven together with a no-clean flux formula added to it to increase absorption.

Removes up to four times more solder than conventional wick, and extracts solder much faster than wicks based on Type-R fluxes.

Residue left behind is halide free and non-conductive, so it does not have to be cleaned off the board.

100% copper wick has fine braid design to promote strong capillary action to pull in excess solder.

Available with standard or anti-static bobbins.

Solder	
Part No.	Description
SW01-5	No-Clean Wick, #3 Green, Width .075" (1.9mm), Length 5 ft.
SW01-25	No-Clean Wick, #3 Green, Width .075" (1.9mm), Length 25 ft.
SW02-5	No-Clean Wick, #4 Blue, Width .098" (2.5mm), Length 5 ft.
SW02-10	No-Clean Wick, #4 Blue, Width .098" (2.5mm), Length 10 ft.
SW02-25	No-Clean Wick, #4 Blue, Width .098" (2.5mm), Length 25 ft.
SW02-50	No-Clean Wick, #4 Blue, Width .098" (2.5mm), Length 50 ft.
SW03-5	No-Clean Wick w/Anti-Static Bobbin, #3 Green, Width .075" (1.9mm), Length 5 ft.
SW03-10	No-Clean Wick w/Anti-Static Bobbin, #3 Green, Width .075" (1.9mm), Length 10 ft.
SW03-25	No-Clean Wick w/Anti-Static Bobbin, #3 Green, Width .075" (1.9mm), Length 25 ft.
SW04-5	No-Clean Wick w/Anti-Static Bobbin, #4 Blue, Width .098" (2.5mm), Length 5 ft.
SW04-10	No-Clean Wick w/Anti-Static Bobbin, #4 Blue, Width .098" (2.5mm), Length 10 ft.
SW04-25	No-Clean Wick w/Anti-Static Bobbin, #4 Blue, Width .098" (2.5mm), Length 25 ft.
SW04-50	No-Clean Wick w/Anti-Static Bobbin, #4 Blue, Width .098" (2.5mm), Length 50 ft.